



## 5349560-5 Product Details



**5349560-5**

TE Internal Number: 5349560-5

**Active**

### Fiber Optic Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Single Fiber
- Cable Assembly
- ST Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | 
 [Request Sample](#) | 
 [Find Similar Products](#) | 
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [FOMM50 LEAD 2,5S ST - ST](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Designation](#) = Single Fiber
- Product Type = Cable Assembly
- [Fiber Optic Cable Connector Type](#) = ST
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)
- Cable Type = Simplex

#### Electrical Characteristics:

- Insertion Loss (dB) = 0.30

#### Termination Features:

- [Fiber Type \(Micron\)](#) = 50/125

#### Dimensions:

- Cable Diameter (mm [in]) = 2.50 [.098]
- Length (M [ft]) = 5.00 [16.40]

#### Body Features:

- Cable Color = Orange
- Boot Body Style - Left = Standard
- Boot Color - Left = Black
- Boot Body Style - Right = Standard
- Boot Color - Right = Black
- Ferrule Material = Ceramic

#### Contact Features:

- Fibre Channel = No

#### Configuration Features:

- [Mode](#) = Multimode
- Number of Fibers = 1
- Cable Buffering = Tight Buffered Easy Strip
- Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

#### Industry Standards:

- Flammability Rating Type = LSZH (Low Smoke Zero Halogen)
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Product Availability:

- Region = Not Specified

#### Other:

- Brand = AMP

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)  
[AODA Accessibility Policy](#)  
[AODA Multi-Year Accessibility Plan](#)

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

