

SlimLINER Fixture

Low-profile outdoor linear lighting



SlimLINER Fixture offers natural white illumination for awnings and wall washes.

Low-profile, exterior building illumination:

- Awning
- Vinyl canopy
- Accent lighting

SlimLINER Fixture can be used in applications traditionally reserved for Slim T4 and T5 fluorescent fixtures—with a much slimmer profile. It is easy to install with peel-n-stick tape or included mounting clips and can be cut in the field to custom lengths. The sleek, slender design of the SlimLINER Fixture is ideal for awnings and cove applications.

Specifications

Part number	701956-5WL461	
Dimensions L × W × H	46 in × 0.875 in × 0.375 in	
Lumens per fixture	725	
Nominal color temperature	5000 K	
Color Rendering Index (CRI)	70 (nominal)	
Estimated product lifetime	50,000 hours (L ₇₀)	
Operating temperature	-40° C to +70° C	
Protection class	IP68	
Special feature	Cuttable every 6 inches	
Power	Per foot	Per stick
	2.25 W	9 W
Efficacy	83.3 lm/W	
Fastening	Peel-n-stick or mounting clips (PN 401203), 4 included with each unit	
Power capacity	6 units per SloanLED 60 W 12 VDC power supply	
Product warranty	5-year limited	

