



EXTREME DEWALT® Cobalt Bit Sets

Selling Proposition

- Precision ground twist drill manufactured to DIN 338. Right hand cutting helix, type N flute.
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling arduous materials.
- Unique Extreme Cobalt tip improves efficiency and eliminates walking.
- Finish - Gold Ferrous

Applications

- Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

Warranty Specifications

- 12 months warranty

Specifications



Cat. No. & Product Description	Description	Diameters mm	Pack Quantity	M.O.Q.	
DT5940	HSS-Co DIN 338 Cobalt Drill Bit Sets	6 piece set in plastic cassett	2, 3, 4, 5, 6, 8 mm	6	1
DT7942	Small tough case with EXTREME DEWALT Cobalt bits		1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4	12	1
DT5928	HSS-Co DIN 338 Cobalt Drill Bit Set	29 piece set	1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.	29	1