

## Chassis Handles *1427 Series*

### Features

- Material is round steel.
- Available in Chrome Plated or Black Powder Coated.
- Sold individually or in pairs (see table).
- Hardware included.



Chrome Part No. (Sold Individually)	Black Part No. (Sold Individually)	Black Part No. (Sold in Pairs)	Handle Mounting Hole Centers	Handle Depth	Handle Diameter	Screw Thread	Panel Height
<b>1427B</b>			1.25	0.62	0.19	4-40	1.75
<b>1427B2</b>	<b>1427B2BK-1</b>	<b>1427B2BK</b>	1.25	1.00	0.19	6-32	1.75
<b>1427D</b>			1.75	0.75	0.19	4-40	5.25
<b>1427E</b>	<b>1427E1BK-1</b>	<b>1427E1BK</b>	2.00	1.00	0.19	6-32	5.25
<b>1427Q</b>			2.30	0.95	0.25	6-32	5.25
<b>1427P</b>	<b>1427P1BK-1</b>	<b>1427P1BK</b>	2.80	1.00	0.25	6-32	5.25
<b>1427G2</b>	<b>1427G2BK</b>		3.00	1.00	0.19	4-40	8.75
<b>1427G3</b>	<b>1427G3BK</b>		3.00	1.50	0.31	10-32	8.75
<b>1427G</b>			3.00	1.75	0.25	8-32	8.75
<b>1427N</b>	<b>1427N1BK</b>		3.50	1.20	0.38	10-32	8.75
<b>1427N2</b>	<b>1427N2BK</b>		3.50	1.50	0.25	8-32	8.75
<b>1427C1</b>	<b>1427C1BK</b>		4.00	1.30	0.38	10-32	8.75
<b>1427S3</b>	<b>1427S3BK</b>		4.00	1.50	0.31	10-32	8.75
<b>1427S</b>			4.00	1.50	0.25	8-32	8.75
<b>1427S2</b>			4.00	1.75	0.25	8-32	8.75
<b>1427U3</b>	<b>1427U3BK</b>		4.50	1.50	0.31	10-32	8.75
<b>1427T3</b>	<b>1427T3BK</b>		5.00	1.50	0.31	10-32	12.25
<b>1427T</b>			5.00	1.50	0.25	8-32	12.25
<b>1427T2</b>			5.00	1.75	0.25	8-32	12.25
<b>1427M</b>	<b>1427M1BK</b>		5.30	1.20	0.38	10-32	12.25
<b>1427W</b>			6.00	1.50	0.25	8-32	12.25
<b>1427W3</b>	<b>1427W3BK</b>		6.00	1.75	0.31	10-32	12.25
<b>1427W2</b>			6.00	1.75	0.25	8-32	12.25
<b>1427L</b>	<b>1427L1BK</b>		7.00	1.30	0.38	10-32	14.00

*Data subject to change without notice*

