










## Series 7400 Kraftform adjustable torque screwdrivers with Rapidaptor quick-release chuck



- Application:** Suitable for 1/4" DIN 3126-C 6.3 and E 6.3 (ISO 1173) hexagon insert bits and Wera Series 1 and 4
- Design:** Rapidaptor rapid-in, rapid-out, rapid-spin, chuck-all and single-hand technology
- Accuracy:**  $\pm 6\%$  (EN ISO 6789). Numerical torque value scale, audible excess-load signal
- Handle:** Kraftform with non-roll feature, multi-component

								
Code	Art.No.	mm	1/4"	Nm	Nm	mm	6"	1
05074700001	7440	105	1/4"	0.3-1.2	0.05	155	6"	1
05074701001	7441	105	1/4"	1.2-3.0	0.10	155	6"	1