

General Information

Extended Product Type:	CE4T-10R-01
Product ID:	1SFA619550R1041
EAN:	7320500260715
Catalog Description:	CE4T-10R-01 EMERGENCY STOP
Long Description:	Compact Emergency Stop

Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

Ordering

EAN:	7320500260715
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.030 m
Product Net Height:	0.040 m
Product Net Depth:	0.073 m
Product Net Weight:	0.036 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	0.1 m
Package Level 1 Height:	0.04 m
Package Level 1 Length:	0.1 m
Package Level 1 Gross Weight:	0.036 kg

Environmental

Ambient Air Temperature:	Operation -25 ... +70 °C Storage -30 ... +85 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Actuator Type:	Mushroom 40mm
Bezel Material:	Black plastic
Color:	Red
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Function:	Twist release
Illumination:	Non-illuminated
Mechanical Durability ():	0.5 million
Number of Auxiliary Contacts NC:	1
Product Main Type:	CE4T
Product Name:	EMERGENCY STOP
Product Range:	Compact
Rated Frequency (f _r):	Supply Circuit 50 Hz Supply Circuit 60 Hz
Rated Operational Current AC-15 (I _e):	(220 / 240V) 1 A (24 / 127V) 1.5 A
Rated Operational Current DC-13 (I _e):	(125V) 0.2 A (24V) 0.3 A
RoHS Date:	0626 5

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-82;
---------------------------------	---------------------------

Classifications

E-number:	3711514
ETIM 4.0:	EC002611 - Control switch
ETIM 5.0:	EC002611 - Control switch
Object Classification Code:	S
UNSPSC:	39121500

