

CR-M024DC2



General Information

Extended Product Type:	CR-M024DC2
Product ID:	1SVR405611R1000
EAN:	4013614497223
Catalog Description:	CR-M024DC2 Pluggable interface relay
Long Description:	The CR-M024DC2 pluggable interface relay is from the CR-M (miniature) relay range. This relay operates with a 24 V DC rated control supply voltage and has a 2 c/o (SPDT) output with contacts rated at 250 V / 12 A. The relay has an integrated blue test button for manual actuation and locking of the output contacts. Standard sockets, logic sockets, pluggable function modules, holder and marker are available as accessories.

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

EAN:	4013614497223
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900

Dimensions

Product Net Width:	21.2 mm
Product Net Height:	35.6 mm
Product Net Depth:	27.5 mm
Product Net Weight:	0.033 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	114.0 mm
Package Level 1 Height:	61.0 mm
Package Level 1 Length:	50.0 mm
Package Level 1 Gross Weight:	0.350 kg
Package Level 1 EAN:	4013614373145

Technical

Function:	Pluggable miniature interface relay CR-M
Sub-Function:	Relay w/o built in LED
Output:	2 c/o (SPDT) contacts
Output Signal:	250 V / 12 A
Rated Control Supply Voltage (U_g):	24 V DC

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

CCC Certificate:	CCC_2014010303720193
-------------------------	----------------------

CSA Certificate:	CSA_2735700
cUR Certificate:	cUR_E244330
Declaration of Conformity - CE:	1SAD938501-0159
EAC Certificate:	EAC_RU_C-PL.ME77.B.01873
GOST Certificate:	GOST_POCC_DE.AB76.D02256
RMRS Certificate:	RMRS_12.04008.250
RoHS Information:	1SAA981040-4404
UR Certificate:	UR_E244330
VDE Certificate:	VDE_40040327

Classifications

Object Classification Code:	K
E-nummer:	4005332
ETIM 4.0:	EC001437 - Switching relay
ETIM 5.0:	EC001437 - Switching relay
UNSPSC:	39121500
eClass:	7.0 27371601
