

## DB16E

ABB contact for United  
States of America



### General Information

---

<b>Extended Product Type:</b>	DB16E
<b>Product ID:</b>	1SAX101110R0001
<b>EAN:</b>	4013614332814
<b>Catalog Description:</b>	DB16E Single Mounting Kit
<b>Long Description:</b>	DB16E Single Mounting Kit for E16DU

---

### Categories

---

Products » Low Voltage Products and Systems » Control Products » Contactors » Electronic Overload Relays Accessories

---

### Ordering

---

<b>EAN:</b>	4013614332814
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85389099

---

### Dimensions

---

<b>Product Net Width:</b>	44.3 mm
<b>Product Net Height:</b>	91.0 mm
<b>Product Net Depth:</b>	65.2 mm
<b>Product Net Weight:</b>	0.035 kg

---

### Container Information

---

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	99.0 mm
<b>Package Level 1 Height:</b>	82.0 mm
<b>Package Level 1 Length:</b>	48.0 mm
<b>Package Level 1 Gross Weight:</b>	0.055 kg
<b>Package Level 2 Units:</b>	48 piece
<b>Package Level 2 Width:</b>	288.0 mm
<b>Package Level 2 Height:</b>	210 mm
<b>Package Level 2 Length:</b>	395.0 mm
<b>Package Level 2 Gross Weight:</b>	3.026 kg
<b>Package Level 2 EAN:</b>	4013614442414

---

### Technical

---

<b>Suitable For:</b>	E16DU
<b>Standards:</b>	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508 CSA 22.2 No. 14

---

### Environmental

---

<b>Ambient Air Temperature:</b>	Operation -25 ... +70 °C Storage -25 ... +70 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

**Certificates and Declarations (Document Number)**

---

<b>cUL Certificate:</b>	cUL_E48139
<b>Declaration of Conformity - CE:</b>	1SAD938508-0053
<b>GOST Certificate:</b>	1SAA941000-2704
<b>RoHS Information:</b>	1SAA964002-4401
<b>UL Certificate:</b>	UL_E48139

---

**Classifications**

---

<b>Object Classification Code:</b>	Q
<b>eClass:</b>	7.0 27379201
<b>ETIM 4.0:</b>	EC002498 - Accessories for low-voltage switch technology
<b>ETIM 5.0:</b>	EC002498 - Accessories for low-voltage switch technology
<b>UNSPSC:</b>	39120000

---

