



## SNA Terminal Blocks

### T&B Catalog Number:

012547925

**UPC Number:**

66201995904

**Status:**

Active

**Description:**

Blue feed through multiclamp terminal block with 6 mm spacing and 20 amp rated UL current with screw clamp connection

### Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Blue
Mounting	DIN 3
Series	M 4/6.4A.N
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	0.2 - 4
Rated IEC Wire Range (Stranded) (mm <sup>2</sup> )	0.22 - 4

### Dimension Information

L x W x H (mm)	63.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	2.50 x 2.38 x 2.09
Spacing (inches)	0.236

### Specifications

UL Current (Amps)	20
UL Voltage (VAC)	600

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	3.5 lbs. per 100

### Certifications

Approvals	UL
-----------	----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)