

JB & WM Accessories

Support Rails—TS 35/7.5 and TS 35/15

For enclosure width in inches (mm)	Support rails length in inches (mm)	Description	PU	Part No.	JB	WM
6 (150)	5 (137)	TS 35/7.5	10	2314.000	■	■
8 (200)	7 (187)		10	2315.000	■	■
12 (300)	11 (287)		10	2316.000	■	■
16 (400)	15 (387)		10	2317.000	–	■
20 (500)	19 (487)	TS 35/15	10	2318.000	–	■
24 (600)	23 (587)		10	2319.000	–	■

Rails for Interior Installation

Enclosure Depth in inches (mm)	PU	Part No. Carbon Steel	JB	WM
8 (210)	4	2383.210	–	■
10 (250)	4	2383.250	■	■
12 (300)	4	2383.300	–	■

Window Kits

Window Height in inches (mm)	Window Width in inches (mm)	Frame Height in inches (mm)	Frame Width in inches (mm)	Part No. Carbon Steel	Part No. Type 304 Stainless Steel	Part No. Type 316L Stainless Steel	JB	WM
5 (127)	3 (76)	8 (191)	6 (140)	WK0503C	WK05034	WK05036	■	■
9 (229)	6 (140)	12 (292)	8 (203)	WK0905C	WK09054	WK09056	■	■
13 (330)	3 (76)	16 (394)	6 (140)	WK1303C	WK13034	WK13036	–	■
13 (330)	8 (203)	16 (394)	11 (267)	WK1308C	WK13084	WK13086	–	■
17 (432)	6 (140)	20 (495)	8 (203)	WK1705C	WK17054	WK17056	–	■
17 (432)	11 (279)	20 (495)	14 (343)	WK1711C	WK17114	WK17116	–	■
23 (584)	15 (381)	26 (648)	18 (445)	WK2315C	WK23154	WK23156	–	■
29 (737)	19 (483)	32 (800)	22 (546)	WK2919C	WK29194	WK29196	–	■
35 (889)	23 (584)	38 (953)	26 (648)	WK3523C	WK35234	WK35236	–	■

Dead Front Kits

Enclosure Height in inches (mm)	Enclosure Width in inches (mm)	Part No. Carbon Steel	JB	WM
12 (305)	12 (305)	DFK1212C	–	■
16 (406)	12 (305)	DFK1612C	–	■
16 (406)	16 (406)	DFK1616C	–	■
16 (406)	20 (508)	DFK1620C	–	■
20 (508)	16 (406)	DFK2016C	–	■
20 (508)	20 (508)	DFK2020C	–	■
20 (508)	24 (610)	DFK2024C	–	■
24 (610)	16 (406)	DFK2416C	–	■
24 (610)	20 (508)	DFK2420C	–	■
24 (610)	24 (610)	DFK2424C	–	■
24 (610)	30 (762)	DFK2430C	–	■
30 (762)	20 (508)	DFK3020C	–	■
30 (762)	24 (610)	DFK3024C	–	■
30 (762)	30 (762)	DFK3030C	–	■
36 (914)	24 (610)	DFK3624C	–	■
36 (914)	30 (762)	DFK3630C	–	■
36 (914)	36 (914)	DFK3636C	–	■
42 (1067)	30 (762)	DFK4230C	–	■
42 (1067)	36 (914)	DFK4236C	–	■
48 (1219)	36 (914)	DFK4836C	–	■
60 (1524)	36 (914)	DFK6036C	–	■
72 (1829)	36 (914)	DFK7236C	–	■