



-1. Wrenches

-1.1. ADJUSTABLE WRENCHES

- Adjustable wrenches developed according to the scientific ERGO™ process
- Standards: ISO 6787, DIN 3117, ASME B107.8M - 1996 and BS 6333
- High performance alloy steel
- Comfortable non slip thermoplastic grip handle
- Scale in mm for pre adjusting and accurate measurement
- The jaw does not fall out even at maximum opening of the wrench
- Head angle 15° provides better accessibility
- Left-handed screw
- P series: Reversible jaw for pipe use
- Black finish. Precision hardened and anti-corrosion treated

90 series

90



			A mm	B mm	C mm	D mm	
9070	7314150100170	5	158	20	4.9	11.3	139
9070 P	7314150103416	5	158	21	4.9	11.3	139
9071	7314150100194	5	208	27	6.0	12.9	272
9071 P	7314150103430	5	208	28	6.0	12.9	272
9072	7314150055609	5	257	31	8.7	15.2	425
9072 P	7314150056354	5	257	33	8.7	15.2	430
9073	7314150101702	5	308	34	11.9	17.6	730
9073 P	7314150101726	5	308	35	11.9	17.6	745

