



Representative

Catalog Number: B 906 10
Product ID: 7TAA004210R0000
UPC Number: 78599175528
EAN Number: 05414363129318
Status: Active

Channel, 14 Gauge, 1-1/2 Inch x 3/4 Inch, Length 10 Feet, Steel

- Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
- The 1-1/2 Inch dimension in the channel, hole spacing and fittings means all parts fit together, no matter where they are used, or at what angle.
- The modular dimension provides maximum flexibility in field applications and results in saving inventory and labor dollars
- Even though Kindorf channel is slightly smaller in dimensions it supports the same weight as 1-5/8 Inch channel.
- The Kindorf system is designed so that most accessories are compatible with 1-5/8 Inch strut. Conduit and pipe straps will work equally well with 1-5/8 Inch and 1-1/2 Inch strut.
- 98 percent of 1-5/8 Inch accessories are interchangeable in Kindorf channel.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

| | |
|----------------------|---|
| UNSPSC | 30101804 Steel channels |
| IGCC | 2577 Steel channels |
| Brand Name | Kindorf |
| Type | Metal Channels |
| Special Features | Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces. |
| Application | Support and framing applications |
| Length | 10 Feet |
| Width | 1-1/2 Inch |
| Depth | 3/4 Inch |
| Gauge | 14 Gauge |
| Material Composition | Steel |
| Finish | Gold |

European Specifications (ETIM)

| | |
|---------------------|-------------------------------|
| ETIM | EC000386 Support/profile rail |
| Profile shape | U-profile |
| Model | Simple profile |
| Type of perforation | None |
| With tothing | N |
| Snap-off | N |
| Material | Steel |
| Material quality | Other |
| Colour | None |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 10 |
| Inner Dimensions (inches) | 120x1.5x.75 |
| Outer Quantity | 600 |
| Outer Dimensions (inches) | 120x11.5x4.19 |
| Weight Uom | 75 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| SDS US 1 | sds-00046-tb2 |
| Technical Data Sheet US | Available on Website |
| Instruction Sheet 1 | ta04629-tb2 |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com