

**Options — Factory Installed**

To order C25, C65, A25 and B25 Contactors and Starters with the factory installed options listed below, change the basic Catalog Number listed in the Product Selection Table as noted.

**Table 35-14. Factory Installed Options**

Description	Code Letter	Number of Poles	Adder U.S. \$
<b>Terminals — 15A through 50A</b>			
<b>Binding Head Screws</b>			
Without Quick Connect Terminals	<b>A</b>	2-, 3-, 4-Pole	
With Quick Connect Terminals (Side-by-Side)	<b>B</b>	2-, 3-, 4-Pole	
With Quick Connect Terminals (Vertical In-Line)	<b>G</b>	2-, 3-Pole	
<b>Screw/Pressure Plate</b> ②			
Without Quick Connect Terminals	<b>C</b>	2-, 3-, 4-Pole	
With Quick Connect Terminals (Side-by-Side)	<b>D</b>	2-, 3-, 4-Pole	
With Quick Connect Terminals (Vertical In-Line)	<b>H</b>	2-, 3-Pole	
<b>Box Lugs</b>			
<b>(#2 Posidrive/Slotted Screw)</b>			
Without Quick Connect Terminals	<b>E</b>	2-, 3-, 4-Pole ①	
With Quick Connect Terminals (Side-by-Side)	<b>F</b>	2-, 3-, 4-Pole ①	
With Quick Connect Terminals (Vertical In-Line)	<b>J</b>	2-, 3-Pole	
<b>Box Lugs (Hex Socket Allen Head Screw)</b>			
Without Quick Connect Terminals	<b>K</b>	2-, 3-Pole	
With Quick Connect Terminals (Side-by-Side)	<b>L</b>	2-, 3-Pole	
With Quick Connect Terminals (Vertical In-Line)	<b>M</b>	2-, 3-Pole	
<b>Terminals — 60A through 75A</b>			
Replace letter in the 6th position of Catalog Number with Code Letter listed below. EXAMPLE: Change C25FNF250 to C25FNE250.			
<b>Box Lugs (Slotted Screw)</b>			
Without Quick Connect Terminals	<b>E</b>	2-, 3-Pole	
With Quick Connect Terminals	<b>F</b>	2-, 3-Pole	

① 4-Pole contactors have box lugs with slotted screws.  
② Screw/Pressure Plate terminals are not available on 50A Contactors.

**Auxiliary Contacts (Side Mount)**

**Table 35-15. Auxiliary Contacts — Factory Installed**

Add Code Letter listed below to complete Catalog Number. EXAMPLE: Change C25DND215A to C25DND215AA.

Description	With Standard Pressure Plate Terminals		With Quick Connect Terminals		Snap Switch Design with Quick Connect Terminals	
	Code Letter	Adder U.S. \$	Code Letter	Adder U.S. \$	Code Letter	Adder U.S. \$
<b>For 15 through 90A</b> ③						
1NO	<b>A</b>		<b>F</b>		—	
1NC	<b>B</b>		<b>G</b>		—	
1NO-1NC	<b>C</b>		<b>H</b>		—	
2NO	<b>D</b>		<b>J</b>		—	
2NC	<b>E</b>		<b>K</b>		—	
<b>For 15 through 75A</b>						
1NO-1NC	—		—		<b>L</b>	
2NO-2NC	—		—		<b>M</b>	
<b>For 120 through 360A</b>						
1NO	<b>A</b>		—		—	
1NO-1NC	<b>C</b>		—		—	
2NO	<b>D</b>		—		—	
2NC	<b>E</b>		—		—	

**Special Marking**

Special contactor marking, consult local sales office.

③ 90A available only with binding head screw and quick connect terminals.

**Accessories**

**Auxiliary Contact Kits (Side Mounted)**



*Side Mounted Auxiliary Contact*

**Table 35-16. Heavy-Duty Pilot Rated for 10A at 600V AC**

Circuit	With Standard Pressure Plate Terminals		With Pressure Plate and Quick Connect Terminals	
	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$
<b>For 15 through 75A</b>				
1NO	<b>C320KG1</b>		<b>C320KG11</b>	
1NC	<b>C320KG2</b>		<b>C320KG12</b>	
1NO-1NC	<b>C320KG3</b>		<b>C320KG13</b>	
2NO	<b>C320KG4</b>		<b>C320KG14</b>	
2NC	<b>C320KG5</b>		<b>C320KG15</b>	
<b>For 90A</b>				
1NO	—		<b>C320DPG10</b>	
1NC	—		<b>C320DPG01</b>	
1NO-1NC	—		<b>C320DPG11</b>	
2NO	—		<b>C320DPG20</b>	
<b>For 120 through 360A</b>				
1NO	<b>C320KGS20</b>		—	
1NC	<b>C320KGS21</b>		—	
1NO-1NC	<b>C320KGS22</b>		—	



*Side Mounted Snap Switch*

**Table 35-17. Snap Switch Design Side Mounted Auxiliary Contacts**

Circuit	Snap Switch Design with Quick Connect Terminals	
	Catalog Number	Price U.S. \$
1NO-1NC 2NO-2NC	<b>C320SNP11</b> <b>C320SNP22</b>	

15 – 360A, Options and Accessories

**Magnet Coil Quick Connect Terminal**

Table 35-18. Magnet Coil Quick Connect Terminal

Description	Adder U.S. \$
Extra Dual Quick Connect Terminals (U-shaped) for Magnet Coil Terminals ①	

① To order, add Suffix Number 9 to the complete Catalog Number. Example: C25DND215A9.

35

**Auxiliary Contact Kits (Top Mounted)**



Top Mounted  
Auxiliary Contact

Table 35-19. Heavy-Duty Pilot Rated for 10A at 600V AC

Circuit	With Standard Pressure Plate Terminals	
	Catalog Number	Price U.S. \$
1NO 1NC	C320KGT1 C320KGT2	
1NO-1NC 2NO 2NC	C320KGT3 C320KGT4 C320KGT5	
3NO 2NO-1NC 1NO-2NC 3NC 4NO	C320KGT9 C320KGT10 C320KGT11 C320KGT12 C320KGT13	
3NO-1NC 2NO-2NC 1NO-3NC 4NC	C320KGT14 C320KGT15 C320KGT16 C320KGT17	

For 15 through 75A ②

② Not available for 4-pole contactors (15 – 40 Amp).

**Mechanical Interlock Kit**



Mechanical  
Interlock

Table 35-20. Mechanical Interlock Kit for 15 through 75A

Catalog Number	Price U.S. \$
C321KM60B	

**Solid-State ON DELAY Timer**



Solid-State  
ON DELAY Timer

**Side Mounted on C25D, C25E and C25F Frame**

This timer is designed to be **wired in series with the load** (typically a coil). When the START button is pushed (power applied to timer), the ON DELAY timing function starts. At the completion of the set timing period, timer and series wired load will both be energized.

Table 35-21. Solid-State ON DELAY Timer

Timing Range	Catalog Number ③④⑤	Price U.S. \$
.1 – 1.0 Seconds	C320TDN1_	
1 – 30 Seconds	C320TDN30_	
30 – 300 Seconds	C320TDN300_	
5 – 30 Minutes	C320TDN3000_	

③ Add operating voltage Suffix to Catalog Number. A = 120V, B = 240V, E = 208V

④ Rated .5 ampere pilot duty — not to be used on larger contactors.

⑤ Terminal connections are quick connects only. Two per side.

**Separate Enclosures**



NEMA 1 Enclosure —  
Cat. No. C799B19

Table 35-22. Separate Enclosures — NEMA 1

Application	Catalog Number	Price U.S. \$
15 through 50A, 2- and 3-Pole	C799B18	
60A, 2- and 3-Pole or 25 through 40A, 4-Pole	C799B19	