

## RJ45FC6-ORN

Article Number: 852-25073

Category 6 Modular Keystone Jack, Orange, 1/bag



Download drawing



Download spec sheet

### Base Data

**Local Order Number** RJ45FC6-ORN

**Type** RJ45FC6-ORN

**Color** Orange (OG)

- Features and Benefits**
- Category 6 jack has been uniquely designed adopting HellermannTyton's globally tried and tested 10-Pin technology which guarantees superior performance and connectivity.
  - Standard keystone style interface provides flexibility in connecting components.
  - Unique strain relief design secures cable terminations.
  - Configured to both TIA 568A and 568B wiring schemes for installation versatility.
  - Available in 12 colors for easy color coding identification

**Product Description** HellermannTyton's GigaBand flush Category 6 modular jack is designed to "future proof" installations. Its patented design uses innovative crosstalk-cancellation technology. The performance of the GigaBand system provides significant margin over TIA Category 6 (ANSI/TIA-568-C.1) and ISO Class E (ISO/IEC-11801, 2nd edition) requirements. The GigaBand system will easily support applications such as Gigabit Ethernet. ETL tested and approved for Category 6 component compliance.

**Technical Description** The performance of the Cat6 system provides significant margin over TIA Cat6 and ISO/IEC 11801 requirements.

**Short Description** Category 6 Modular Keystone Jack, Orange, 1/bag

### Product Dimensions

**Performance Category** Category 6 (Class E)

**Port count** 1

**Width W (Imperial)** 7.75 "

**Width W (Metric)** 19.0 mm

**Height H (Imperial)** 7.91 "

**Height H (Metric)** 23.0 mm

**Depth D (imperial)** 1.65 "

**Depth D (metric)** 42.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity** 1

**Package Quantity (Metric)** 1

**Carton Quantity** 50

### Material and Specifications

