

Series **Durable Pressure Switch** Designed for Extended Duty, Simple and Reliable

1/4" NPT

#8-32 SCREW

TERMINALS

ø1-1/2 [ø38.1]

2-5/16

[58.74]

 (\bigcirc)

A-440



Series A6 Durable Pressure Switches have been specifically designed to stand up to extended duty applications. These switches are constructed with a polyamide film diaphragm and are compatible with a variety of fluids. For ease of installation, the switches come with a 1/4" male NPT process connection and can be mounted in any orientation. The Series A6 pressure switches are compact and have great setpoint integrity, and feature simple, easy set-point field adjustment.

A-439

A-440

A6

| | Set Point Range psi (bar) | |
|-----------|---------------------------|--------------------------------|
| Model | NC | NO |
| A6-153221 | 0.5 to 1 (0.03 to 0.07) | 1.1 to 3.1 (0.08-0.21) |
| A6-253221 | 1.1 to 3 (0.08 to 0.21) | 2.27 to 6.05 (0.16-0.42) |
| A6-353221 | 3.1 to 7 (0.21 to 0.48) | 4.22 to 10.75 (0.29 to 0.74) |
| A6-453221 | 8 to 13 (0.55 to 0.90) | 12.3 to 17.5 (0.85 to 1.21) |
| A6-553221 | 14 to 24 (0.97 to 1.66) | 18.6 to 31.8 (1.28 to 2.19) |
| A6-653221 | 25 to 50 (1.73 to 3.45) | 33.1 to 61 (2.28 to 4.21) |
| A6-753221 | 51 to 90 (3.52 to 6.21) | 65.6 to 112.3 (4.53 to 7.75) |
| A6-853221 | 91 to 150 (6.28 to 10.35) | 114.7 to 198.3 (7.94 to 13.68) |

ACCESSORIES

A-439, Weatherproof IP65 Cover A-440, Weatherproof IP65 with Fly-wire holes

SPECIFICATIONS

2-7/16 [62]

ø1.500

[ø38.1]

Ø

Service: Air, motor oils, transmission oils, jet fuels, and similar hydrocarbon media.

Wetted Materials: Base: 304 SS: Diaphragm: Polyamide film. Temperature Limits: -40 to 248°F (-40 to 120°C).

Pressure Limits: Operating Pressure: 150 psi (10.3 bar) for 0.5-24 psi set point ranges, 250 psi (17.2 bar) for 25 to150 psi set-point ranges; Proof Pressure: 500 psi (34.5 bar); Burst Pressure: 750 psi (51.7 bar) for 0.5-24 psi set point ranges, 1250 psi (86.2 bar) for 25-150 psi set-point ranges. Enclosure Rating: General purpose or with cover: IP65 - weatherproof.

Repeatability: ±10% of set-point. Set Point Tolerance: ±15% of range. Switch Type: 1 SPST NO, 1 SPST NC. NO and NC switch independent from each other.

ø1-1/2 [ø38.1]

2

[50.8]

A-439

Electrical Ratings: Resistive: 15 A @ 6 VDC, 8 A @ 12 VDC, 4 A @ 24 VDC; Inductive: 1 A @ 120 VAC, 0.5 A @ 240 VAC.

Electrical Connections: #8-32 screw terminals.

Process Connection: 1/4" NPT male. Mounting Orientation: Switch can be installed in any position. Set-point Adjustment: Screw. Weight: 0.13 lb (0.06 kg). Agency Approval: CE.