

PNOZ X3P 24VDC 24VAC 3n/o 1n/c 1so

777310



Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 3 N/O, 1 N/C, 1 SC, automatic/monitored start, UB 24 V AC/DC, width: 45 mm, plug-in screw terminals, monitoring of E-STOP, safety gates.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC
Power consumption AC:	5 VA
Power consumption DC:	2.5 W
Inputs	
Number of inputs:	2
Semiconductor outputs	
Number of semicond. outputs:	1
Tolerance ext. volt. DC S/C:	-20 %/+20 %
Utilisation cat. to EN 60947-1:	DC-12
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	8 A
Voltage DC1 safety cont.:	24 V
Max. current DC1 safety cont.:	8 A

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	5 A
Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G. P.
Safety contacts: pilot duty:	B300, R300
Relay contact material:	AgSnO ₂
Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-20 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	24 - 12 AWG
Height dimension:	94 mm
Width dimension:	45 mm
Depth dimension:	121 mm
Net weight:	270 g
Gross weight:	280 g

Environment	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449

Optional accessories



374281

PNOZ X Set plug in screw terminals P3+P4