



ISSUE	REF. NO.	DESCRIPTION	DATE
001	HG04-112-13	FIRST SUBMISSION.	17/04/13

NOTE :

1. ALL DIMENSIONS IN mm.
2. THIS PART CAN BE MANUFACTURED AT ANY LOCATION WHICH HAS SAFETY APPROVAL.
3. THIS CORDSET SHALL COMPLY WITH CHINA RoHS.
4. LABEL DETAILS:
REFER TO LABEL DWG. NO.: VL-0356.
5. PACKAGING QTY : 40 PCS PER CARTON.
6. CARTON BOX MUST HAVE A LABEL/STAMP SAYING : "THIS PACKAGE CONTAINS CORDS HAVING GROUNDING CONDUCTOR WITH GREEN/YELLOW COLOUR INSULATOR, GROUNDING CONDUCTOR WITH BLUE COLOUR INSULATOR AND LIVE CONDUCTOR WITH BROWN COLOUR INSULATOR".

APPROVED SOURCE FOR CABLE

1. BAO HING(SHENZHEN).

APPROVAL MARKING TABLE:

PLUG TYPE	IEC 60320-2-2, EN 60320-2-2-STANDARD SHEET E, GB17465.2
CONNECTOR TYPE	C13
CABLE OUTER DIAMETER	9.30mm(REF.)
TEMPERATURE	75°C
CORDSET RATING(AMP/VOLTAGE)	10A/250V

CUSTOMER APPROVED :

APPROVED BY :	
SIGNATURE :	
APPROVED DATE :	

5	PRINTED LABEL	VL-0356	1
4	8" PE TIE BLK	6310062	1
3	IP40G NL792B BLK	4100017	-
	MOLDED CONNECTOR V1625BS (10A 250V)	V1625BS-ST	1
2	IP40G NL792B BLK	4100017	-
	MOLDED PLUG VAC14LS (10A 250V)	VAC14LS-BK	1
1	H05VV-F 3X1.50+SJT 14/3 75°C BBGY		
	BLK LF (EURO+CCC+IEC-J+UL/CSA)	1220041	1

S/N	DESCRIPTION	ITEM NUMBER	QTY
TITLE : EUROPEAN+CHINESE+NORTH-AMERICAN JUMPER CORDSET (PB FR)		SCALE : N.T.S.	
CUSTOMER : VNA/VOLEX INC		PAGE : 1/1	
CUSTOMER PART NUMBER : 2174H		ISSUE	
Reference Number : 132416/2 (HG04-112-13)		001	
SALES :	QA :	ENGRG :	CHECKED BY :
Date :	Date : 18/04/13	Date : 19/04/13	Date : 17/04/13
DRAWN BY : LI MIN			
Voletex (Asia) Pte Ltd			
Confidential property of Voletex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of voletex asia.			