
## **PX0599** Wiring Instructions

Before using the connector, it is important that these instructions are carefully read and understood to ensure the connector is electrically safe. IF IN DOUBT CONSULT A QUALIFIED ELECTRICIAN.

23mm

## **PX0599 Wiring Instructions**

- 1 Remove cover.
- 2 Strip and prepare cable.



- 3 Thread cable sleeve along cable (trim to suit cable diameter if necessary).
- 4 Connect wires to correct terminals with wire strands between washer and terminal:


Colour	European	Nth American
Live/Line (L)	Brown	Black
Neutral (N)	Blue	White
Earth/Ground ( <del>L</del> )	Green/Yellow	Green

- 5 Fit cable sleeve flange into slot adjacent to cable clamp.
- 6 Tighten cable clamp ensuring cable sheath is beyond cable clamp. Reverse clamp to suit cable diameter.
- 7 Fit cover and tighten screw.

## **Recommended Cable types**

## Cable Construction Typical Cable Types

European:	16A - 3 x 1.5mm <sup>2</sup>	H05VV-F, H05RR-F, H07RN-F
Nth American:	20A - 3 x 12AWG	SJT, SVT



www.bulgin.co.uk

