

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, slot, E6.3-1/4" drive, Size: 0.6 x 3.5 x 70 mm, hardened, suitable for holders as per DIN 3126-F 6.3 / ISO 1173

Illustration shows variant SF-BIT-SL
1.0x5.5-70

Product Features

- Tools for SF-ASD 21 cordless screwdriver in various versions



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	20.0 GRM
Custom tariff number	82079030
Country of origin	Czech Republic

Technical data

Dimensions

Blade thickness	0.6 mm
Blade width	3.5 mm
Blade height	70 mm

General

Color	silver
Type	Bladed
Material	Alloyed tool steel
Test standard	DIN 3126 drive, output 3127-1

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Classifications

eCl@ss

eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040402
eCl@ss 6.0	21040290
eCl@ss 7.0	21040290
eCl@ss 8.0	21040290

ETIM

ETIM 4.0	EC002115
ETIM 5.0	EC002115

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals


Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Drawings

Pictogram

