

# Multimeter - TESTFOX CC-1 - 1212211

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Current pliers multimeter, for DC and AC voltage measurements, AC and DC measurements, and resistance measurements

## Why buy this product

- ✓ They combine the functions of a digital multimeter with those of a current probe
- ✓ Enclosed in compact and practical housing, so ideal for use in cramped conditions
- ✓ All measuring ranges are protected against overload
- ✓ The current probes can be used for voltages of up to 600 V, category III

## Key commercial data

Packing unit	1 pc
GTIN	 4 046356 449809
Weight per Piece (excluding packing)	505.0 g
Custom tariff number	90303100
Country of origin	Taiwan

## Technical data

### Ambient conditions

Degree of protection	IP30
----------------------	------

### General

Color	black
Voltage supply	2 x micro battery 1.5 V, LR03, AAA
Measuring category	CAT III 300 V / CAT II 600 V
Test certificate	IEC/EN 61010-1, DIN VDE 0411
Display scope	4000 digits

## Classifications

### eCl@ss

eCl@ss 4.0	27200312
eCl@ss 4.1	27200301

# Multimeter - TESTFOX CC-1 - 1212211

## Classifications

### eCl@ss

eCl@ss 5.0	27200301
eCl@ss 5.1	27200301
eCl@ss 6.0	27200301
eCl@ss 7.0	27200301
eCl@ss 8.0	27200301

### ETIM

ETIM 3.0	EC000069
ETIM 4.0	EC000380
ETIM 5.0	EC000380

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Approvals

### Approvals

---

#### Approvals

VDE Zeichengenehmigung / GOST

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

VDE Zeichengenehmigung
------------------------

GOST
------

