

Aluminium Electrolytic Capacitors

CCC-13

(1 Flap FL16/20) 16 Values / 270 Pieces
Cylindrical Aluminium-Can with radial leads

Type/Brand: RSM 2222 037 xxxxx / PHILIPS or alternative

Tolerance: ±20%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0 uF/63V	40x	22 uF/50V	25x	100uF/63V	14x	1000uF/16V	6x
2,2 uF/63V	25x	47 uF/25V	25x	220uF/35V	8x	1000uF/35V	4x
4,7 uF/63V	30x	47 uF/50V	25x	470uF/16V	6x	2200uF/35V	3x
10 uF/63V	30x	100uF/16V	20x	470uF/35V	6x	4700uF/16V	3x

CCC-14

(1 Flap FL16/20) 16 Values / 270 Pieces
Cylindrical Aluminium-Can with radial leads

Type/Brand: SE-K / TEAPO or Yageo Europe

Tolerance: ±20%

Temperature: -40 to +105°C

Values-Quantities Selection:

1,0uF/63V	40x	22uF/63V	25x	100uF/63V	14x	1000uF/16V	6x
2,2uF/63V	25x	47uF/25V	25x	220uF/35V	8x	1000uF/35V	4x
4,7uF/63V	30x	47uF/63V	25x	470uF/16V	6x	2200uF/35V	3x
10 uF/63V	30x	100uF/16V	20x	470uF/35V	6x	4700uF/16V	3x

CCC-15

(1 Flap FL16/20) 16 Values / 243 Pieces
Cylindrical Aluminium-Can with axial leads

Type/Brand: AS / PHILIPS or alternative

Tolerance: ±20%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0uF/63V	40x	22uF/63V	20x	100uF/63V	6x	1000uF/16V	4x
2,2uF/63V	30x	47uF/25V	25x	220uF/40V	6x	1000uF/40V	3x
4,7uF/63V	30x	47uF/63V	15x	470uF/16V	6x	2200uF/40V	2x
10 uF/63V	30x	100uF/25V	20x	470uF/40V	4x	4700uF/16V	2x

CCC-16

(1 Flap FL16/20) 16 Values / 655 Pieces
Miniature Cylindrical Aluminium-Can with radial leads (4Æx7, 5Æx7, 6Æx7)

Type/Brand: SS / TEAPO or Yageo Europe

Tolerance: ±20%

Temperature: -40 to +105°C

Values-Quantities Selection:

0,10uF/63V	50x	1,0uF/63V	50x	4,7uF/63V	50x	33uF/ 25V	20x
0,22uF/63V	30x	2,2uF/36V	40x	10uF/ 16V	50x	47uF/ 6,3V	50x
0,33uF/63V	20x	3,3uF/63V	25x	10 uF/35V	50x	47uF/ 16V	50x
0,47uF/63V	50x	4,7uF/25V	50x	22 uF/35V	30x	100uF/6,3V	40x

CKC-LX3**23 Values / 62 Pieces****Snap-In Aluminium Electrolytic Capacitors****Type/Brand:** LX / TEAPO**Voltage:** 200 / 250V**Tolerance:** ±20%**Capacitance:** 150 - 1.000uF**Temperature:** -40 to +85°C**Pitch:** 10mm

Binder: CSO-70 (Dimensions: 322x260x70mm) with Styropore-Inlet

Values-Quantities Selection:

150uF/200V (22x25)	4x	220uF/200V (22x30)	3x	330uF/200V (22x35)	3x
220uF/200V (25x25)	3x	330uF/250V (22x45)	4x	470uF/200V (22x45)	4x
220uF/200V (25x25)	3x	220uF/250V (25x30)	2x	330uF/200V (25x30)	3x
470uF/200V (25x40)	3x	470uF/250V (25x45)	3x	680uF/200V (25x50)	2x
330uF/250V (30x30)	3x	680uF/200V (30x35)	4x	680uF/250V (30x50)	2x
820uF/200V (30x45)	2x	1000uF/200V (30x50)	3x	470uF/250V (35x30)	2x
680uF/250V (35x35)	2x	820uF/200V (35x35)	2x	820uF/250V (35x40)	2x
1000uF/200V (35x40)	2x	1000uF/250V (35x45)	2x	680uF/250V (30x50)	2x

CKC-LXK2**19 Values / 62 Pieces****Snap-In Aluminium Electrolytic Capacitors****Type/Brand:** LXK / TEAPO**Voltage:** 250V**Tolerance:** ±20%**Capacitance:** 220-1.200uF**Temperature:** -40 to +85°C**Pitch:** 10mm

Binder: CSO-70 (Dimensions: 322x260x70mm) with Styropore-Inlet

Values-Quantities Selection:

180uF/250V (22x25)	3x	220uF/250V (22x30)	4x	270uF/250V (22x35)	3x
330uF/250V (22x40)	3x	390uF/250V (22x45)	2x	470uF/250V (22x50)	4x
220uF/250V (25x25)	3x	270uF/250V (25x30)	2x	330uF/250V (25x30)	3x
390uF/250V (25x35)	2x	470uF/250V (25x40)	4x	560uF/250V (25x45)	2x
680uF/250V (30x40)	7x	560uF/250V (30x35)	4x	820uF/250V (30x45)	3x
680uF/250V (35x30)	4x	820uF/250V (35x35)	2x		
1000uF/250V (35x40)	4x	1200uF/250V (35x50)	2x		

Chip Aluminium Electrolytic Capacitors

SMC-11

(1 Flap FL16/10) 16 Values / 290 Pieces

High Reliable Aluminium Electrolytic Capacitor in Chip form

Type/Brand: MVK/NCC or alternative

Tolerance: ±20%

Temperature: -40 to +105°C

Values-Quantities Selection:

0,10uF/50V	25x	2,2uF/50V	25x	6,8uF/25V	10x	22uF/25V	10x
0,22uF/50V	25x	3,3uF/50V	15x	10uF/16V	20x	33uF/25V	10x
0,47uF/50V	25x	4,7uF/25V	25x	10uF/50V	20x	47uF/16V	10x
1,0uF/50V	25x	4,7uF/50V	25x	22uF/ 6V	10x	100uF/ 6V	10x