



ENGLISH

Datasheet

RS Pro Automatic Stainless Steel 2kW Hand Dryer, 148mm x 280mm x 270mm

RS Stock No: **612-0986**



Product Details

RS Pro automatic hand dryer measuring 148 x 280 x 270 mm, is made from stainless steel with polished satin finish. It is designed for food preparation areas or hospitals, where high levels of hygiene are required. It has a power rating of 2 kW with a voltage rating of 220 to 240 V.

Features and Benefits

- Satin finish polished stainless steel cover
- Quiet, automatic operation
- IP24 rated
- Powerful 2700 rpm external rotor motor



Specifications:

Air Flow	200 m ³ /h
Automatic/Manual	Automatic
Case Material	Stainless Steel
Depth	148 mm
Finish	Porcelain Enamel
Height	280 mm
Power Rating	2 kW
Supply Voltage	220 to 240 V
Width	270 mm
IP Rating	IP24