

NetController 8-Port Rack-Mount Console KVM Switch w/19-in. LCD

MODEL NUMBER: **B040-008-19**



Description

The B040-008-19 NetController 8-Port Console KVM switch is a cost effective and highly flexible system for controlling multiple computers from a single keyboard, monitor and mouse. Directly connect up to 8 computers, or increase the number of connected computers to up to 248 by daisy chaining up to 15 B042-Series KVM switches. Switch between connected computers via Pushbutton, On Screen Display (OSD), or Hotkey commands. Connect computers to the KVM using a Tripp Lite P780-Series USB/PS2 Combo KVM cable kit. Cable kits come with both USB and PS/2 connectors, allowing you to connect to either a USB or PS/2 computer without the need to purchase additional cables or adapters. Additional VGA and USB ports are located on the back panel of the unit, allowing for the connection of an external VGA monitor and USB keyboard or mouse, or a Tripp Lite B051-000 IP remote access unit.

Password feature provides additional security to prevent unauthorized access to connected computers.

Rackmount hardware is included with the unit, and is designed for easy, one person installation. Fits into any rack from 27 to 42 inches deep, and can be installed in a 2-post rack using Tripp Lite's B019-000. Compatible with all major operating systems. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- 1U rackmount console with built-in 8-Port KVM switch, 19" LCD, keyboard, and touchpad
- Directly control up to 8 computers, or increase the number of connected computers to up to 248 by daisy chaining up to 15 B042-Series KVM switches
- Built-in monitor supports video resolutions up to 1366 X 768
 - Use in racks from 27 to 42 inches deep
- On-Screen Display (OSD) menu for intuitive, easy control of the KVM
- Password protection and auto-log out features
- Firmware upgradeable
- Add IP Remote Access with a Tripp Lite B051-000
- Hot-swappable: disconnect and reconnect USB computers w/o reboot

Highlights

- 1U rackmount console with built-in 8-Port KVM switch, 19" LCD screen, keyboard and touchpad
- Directly control up to 8 computers, or increase the number of connected computers to up to 248 by daisy chaining up to 15 B042-Series KVM switches
- P780-Series USB/PS2 combo KVM cables kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters
- Compatible with all major operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B040-008-19 8-Port, 19" console KVM switch
- 4 ft. HD15 to DB9 firmware upgrade cable
- C13 to 5-15P power cord
- External VGA terminator
- CD with owner's manual and quick start guide
- Quick start guide



- Easy port selection via On Screen Display (OSD), Pushbutton or Hotkey commands
- P780-Series USB/PS2 combo KVM cable kits allow you to connect either USB or PS/2 computers, without the need to purchase additional cables or adapters
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Users	1
Console	Yes
Max CPU	248
INPUT	
Electrical Consumption	(Line Mode) 30W / (Standby Mode) 5W
PHYSICAL	
Color	Black
LCD Monitor (in.)	19
LCD Monitor (cm)	48.26
ENVIRONMENTAL	
Relative Humidity	20% to 90% (non-condensing)
Operating Temperature	32 to 104 F (0 to 40 C)
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.06 BTU/Hr
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	No
CONNECTIONS	
Ports	8
Computer/Server Ports	(x8) HD15 Female
Daisy-Chain Port	HD15 Female
Firmware Upgrade Port	HD15 Male
PC/Server Connections	PS/2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
Cat5 KVM Switch	No
CERTIFICATIONS	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1
Approvals	TUV (UL), CTUV, CE, FCC, NOM, RoHS
NIAP-Certified Secure	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.