

4000-20M04K999 Product Details

 [Live Product Chat](#)



4000-20M04K999

(4-1611450-4)

TE Internal Number: 4-1611450-4

 [Active](#)

Transformers

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- 4000-Class 2 [UL 5085-3] Series
- Primary Voltage = 120 VAC
- Secondary Voltage = 12 VAC
- Transformer Rating = 30 VA
- Mount Style = Foot

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CUSTOMER TRANSFORMER OUTLINE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = Lead
- Size = 19.05 [3/4]

Electrical Characteristics:

- Primary Voltage (VAC) = 120
- Secondary Voltage (VAC) = 12
- [Transformer Rating \(VA\)](#) = 30

Body Related Features:

- [Series](#) = 4000-Class 2 [UL 5085-3]
- [Mount Style](#) = Foot

Configuration Related Features:

- Stack Thickness (mm [in]) = 25.40 [1.000]

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Packaging Related Features:

- Packaging Method = Bulk

Other:

- Brand = Products Unlimited

[Provide Website Feedback](#) | [Need Help?](#)