

Test adapter - PAI-4-FIX BK - 3032774

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



4 mm test adapter, for terminal blocks with 8.2 mm pitch

Why buy this product

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 280358
Weight per Piece (excluding packing)	2.16 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Height	51.50 mm
Diameter	5.80 mm

General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
	Do not plug in while the power is connected
Color	black
Material	PA
Minimum temperature	-40 °C
Maximum temperature	125 °C

Test adapter - PAI-4-FIX BK - 3032774

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27440313

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details

EAC

EAC
