



Standard CAT6, 2 Piece High Performance - Round-Solid 3-Prong

106185

Product Overview

This 2 piece system makes terminating CAT6 quick & easy. The staggered loading bar acts as the stopping point for pair separation and maintains wiring configuration. Simply flush cut the conductors and slide assembly into the connector and terminate.

- Eight conductor mod plug with loading bar
 - Liner Bar Part No.: 1041
 - For conductors with an O.D. Range of .040" - 0.44" (1.02/1.12mm)
 - Uses 0.30mm (.012") Contact
 - 3 prong contact for solid conductors only
 - Max cable jacket O.D., .280" / 7.1mm
 - RoHS & UL Compliant
-

Part Numbers

Part #	UPC	Description
106187		Standard CAT6, 2 Piece High Performance - Round-Solid 3-Prong, 25pc clamshell
106188J		Standard CAT6, 2 Piece High Performance - Round-Solid 3-Prong, 100pc Jar
106185		Standard CAT6, 2 Piece High Performance - Round-Solid 3-Prong, 500pc Bag