

## Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet switch, 4 TP RJ45 ports, 1 FO port, 100 Mbps full duplex in SC-D format, single mode fiberglass, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

### Product Features

- Auto negotiation and autocrossing detection simplifies installation and setup
- Local diagnostic indicators with LEDs
- RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps
- 



### Ethernet

### Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	300.0 GRM
Custom tariff number	85176200
Country of origin	Taiwan

### Technical data

#### Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above mean sea level)

# Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

## Technical data

### Ambient conditions

Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above mean sea level)
Noise immunity	EN 61000-6-2

### Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	4 (RJ45 ports)
Connection method	RJ45
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s
No. of ports	1 (SC single mode)
Connection method	SC
Transmission physics	Single-mode fiberglass
Transmission speed	100 MBit/s (full duplex)
Transmission length	25 km (fiberglass with F-G 9/125 0.5 dB/km)
Wavelength	1300 nm

### Function

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
Status and diagnostic indicators	LEDs: U <sub>S</sub> , link and activity per port

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

### Supply voltage

Supply voltage	24 V DC
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	12 V DC ... 48 V DC
Typical current consumption	175 mA (at U <sub>S</sub> = 24 V DC)

### General

Mounting type	DIN rail
Type AX	Block design
Net weight	205 g
Housing material	Aluminum
Noise emission	EN 61000-6-4

# Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

## Classifications

### eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	19030117
eCl@ss 5.1	19030117
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

### UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

---

#### Ex Approvals

UL Listed / cUL Listed / cULus Listed

---

#### Approvals submitted

---

### Approval details

# Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

## Approvals

UL Listed 

cUL Listed 

EAC

EAC

cULus Listed 

## Accessories

### Accessories

#### End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

---

#### Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

## Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

### Accessories

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

---

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

---

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

---

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

---

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

---

## Industrial Ethernet Switch - FL SWITCH SFNB 4TX/FX SM20 - 2891029

### Accessories

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

---

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

---

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

---

### Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

---