

## Plug-in module - RIF-LDP-12-24 DC - 2900939

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with freewheeling diode and yellow LED, polarity: A1+, A2-, input voltage: 12 - 24 V DC  $\pm 20\%$

### Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	4.0 GRM
Custom tariff number	85363010
Country of origin	China

### Technical data

#### Input data

Input voltage range	12 V DC ... 24 V DC $\pm 20\%$
Status display	Yellow LED
Protective circuit/component	Damping diode

### Classifications

#### eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603

#### ETIM

ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC002586

# Plug-in module - RIF-LDP-12-24 DC - 2900939

## Classifications

### UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39121516

## Approvals

### Approvals

---

#### Approvals

UL Recognized / CSA

---

#### Ex Approvals

---

Approvals submitted

---

### Approval details

