

### General Information

Extended Product Type:	JSTD25F
Product ID:	2TLA020007R6000
EAN:	7350024460322
Catalog Description:	JSTD25F Twohand station, 5-pole M12 Male
Long Description:	Two-hand device with JSTD1-B Safeballs. Buttons are side mounted on a 44x88 extruded aluminum profile designed for two-hand applications. Pre-wired to a M12 5-pin connector with protective flanges of the safeballs. Highest level of safety can be achieved when used in conjunction with a JSBR4 safety relay or Pluto Safety PLC.

### Categories

Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Control Devices

### Ordering

EAN:	7350024460322
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365011

### Dimensions

Product Net Width:	0.365 m
Product Net Height:	0.13 m
Product Net Depth:	0.088 m
Product Net Weight:	1.167 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	38.2 m
Package Level 1 Height:	0.14 m
Package Level 1 Length:	0.095 m
Package Level 1 Gross Weight:	1.317 kg

### Safety Information

Performance Level (PL):	Up to e
Safety Category Acc. to ISO 13849-1:	4

### Additional Information

Product Main Type:	JSTD25
Product Name:	Two Hand Safety Control Device

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter10
Declaration of Conformity - CE:	2TLC172023D0201

### Classifications

ETIM 4.0:	EC001260 - Two-hand control device
ETIM 5.0:	EC001260 - Two-hand control device
Object Classification Code:	B

