



## General Information

---

<b>Extended Product Type:</b>	M12-C103
<b>Product ID:</b>	2TLA020056R4000
<b>EAN:</b>	7350024452471
<b>Catalog Description:</b>	M12-C103 10 m cable 8x0.34 female
<b>Long Description:</b>	10 m cable 8 x 0.34 mm <sup>2</sup> + screen with straight M12 female connector.

---

## Categories

---

Products » Low Voltage Products and Systems » Control Products » Safety Products » Cables and Connectors

---

## Ordering

---

<b>EAN:</b>	7350024452471
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85444290

---

## Dimensions

---

<b>Product Net Width:</b>	0.23 m
<b>Product Net Height:</b>	0.02 m
<b>Product Net Depth:</b>	0.23 m
<b>Product Net Weight:</b>	0.478 kg

---

## Container Information

---

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	0.3 m
<b>Package Level 1 Height:</b>	0.02 m
<b>Package Level 1 Length:</b>	0.3 m
<b>Package Level 1 Gross Weight:</b>	0.478 kg

---

## Additional Information

---

<b>Product Main Type:</b>	Cables
<b>Product Name:</b>	Cable

---

## Certificates and Declarations (Document Number)

---

<b>Declaration of Conformity - CE:</b>	NoDecNee
--	----------

---

## Classifications

---

<b>E-nummer:</b>	3861426
<b>ETIM 4.0:</b>	EC000057 - Low voltage power cable
<b>ETIM 5.0:</b>	EC000057 - Low voltage power cable
<b>Object Classification Code:</b>	W

---

No image available