



BCC M434-0000-2A-000-41X475-000 BCC06M4





Display/Operation

Power indicator

no

Electrical connection

Cable diameter D Number of pins

4

4...6 mm

System

Can be fabricated

Electrical data

Rated current (40 °C)

4.0 A

Environmental conditions

Ambient temperature Protection type IEC 60529 -25...85 °C IP67 Material

Material grip

Material contacts

Material cover nut

Brass

Die-cast zinc

PA

Mechanical data

Connection cross-section Tightening torque pigtail Type of wire mounting 0.14...0.75 mm²

0.6 Nm

Screw terminals

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector view

