



Powering Business Worldwide

pe.eaton.com

Eaton Definite purpose control - contactor

C25END430A

UPC:782113542331

Dimensions:

- **Height:** 3.75 IN
- **Length:** 3.38 IN
- **Width:** 2.68 IN

Weight:2 LB

Notes:Resitive Load rating per pole

Warranties:

- 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 30A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 25-40A, four-pole
- **Model:** Contactor
- **Number Of Poles:** Four-pole
- **Resistive Load:** 40A
- **Terminals:** Screw/pressure plate and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25END4 3D Model Xchange](#)
- [C25END4 2D PDF](#)
- [C25END4 3D Inventor](#)
- [C25END4 AutoCAD 2D Footprint \(mm\)](#)
- [C25END4 2D Drawing Xchange](#)
- [C25END4 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - C25END430A](#)



Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.