


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/30/13	D.GRIFFIN



RECOMMENDED
PANEL CUTOUT

NOTES:

MATERIALS:
FLANGE MOUNT ADAPTER: ZINC ALLOY
COUPLER: ABS, UL94V-0
CASING: BRASS
HARDWARE: STAINLESS STEEL

FINISH:
FLANGE MOUNT ADAPTER: NICKEL PLATE
CASING: NICKEL PLATE
COUPLER COLOR: WHITE


1. COUPLER KIT IS SUPPLIED UN-ASSEMBLED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

2. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

KIT CONTAINS:

- 1 - COUPLER (L-COM P/N# TDG1026KS-RC6A)
- 1 - FLANGE ADAPTER (L-COM P/N# ECF-SK-25)
- 2 - #4-40 UNC-2A x 1/4" LG PHILIPS SST SCREW



<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]</p> <p>PROJECTION </p>	APPROVALS	DATE	<p>L-com Global Connectivity</p> <p>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</p>	
	DRAWN BY D.FRISIELLO	10/29/13		
	CHECKED BY D.GUTTADAURO	10/29/13	CATEGORY TELECOM/MODULAR	
	APPROVED BY M.MARTINEZ	10/29/13	PRODUCT DESCRIPTION CAT6A RJ45 SHD RA PNL CPLR KIT	
<p>COLOR VARIATIONS MAY OCCUR</p>	SIZE A	FSCM NO. 43321	DWG. NO. ECF504-SR6A	REV. A
	SCALE: NONE	CAD FILE: ECF504-SR6A.SLDDRW	SHEET 1 OF 1	