3RT1017-1AF02 Page 1

SIEMENS

Product data sheet 3RT1017-1AF02




CONTACTOR, AC-3 5.5 KW/400 V, 1 NC, AC 110 V, 50/60 HZ, 3-POLE, SIZE S00, SCREW CONNECTION

General details:	
Size of the contactor	S00
Number of poles	3
Control circuit:	
Design of activation of the operating mechanism	conventional
Type of voltage	AC
Control supply voltage	
• at 50 Hz / for AC / rated value / minimum	110 V
at 50 Hz / for AC / rated value / maximum	110 V
• at 60 Hz / for AC / rated value / minimum	110 V
• at 60 Hz / for AC / rated value / maximum	110 V
Supply voltage frequency / for auxiliary and control current circuit / rated value	
• minimum	50 Hz
• maximum	60 Hz
Main circuit:	
Number of NC contacts / for main contacts	0
Number of NO contacts / for main contacts	3
Operating current	

3RT1017-1AF02 Page 2

• at AC-3 / at 400 V / rated value	12 A
• at AC-1 / at 400 V / rated value	22 A
Service power	
• at AC-3 / at 400 V / rated value	5.5 kW
• at AC-1 / at 400 V / rated value	13 kW
Auxiliary circuit:	
Identification number and letter for switching elements	01
Number of NO contacts / for auxiliary contact	0
Number of NC contacts / for auxiliary contact	1
Connection type:	
Design of the electrical connection / for main current circuit	screw-type terminals
Design of the electrical connection / for auxiliary and control current circuit	screw-type terminals
Mounting/fixing:	
Type of fixing/fixation	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022

3RT1017-1AF02 Page 3



last change: 10/31/2006

Technical Assistance:	Telephone:	+49 (0) 911-895-5900 (8°° - 17°° CET)
	Fax:	+49 (0) 911-895-5907
	E-Mail:	technical-assistance@siemens.com
	Internet:	www.siemens.de/lowvoltage/technical-assistance