

SIEMENS

Product data sheet

3RU1116-1JC1



Abb. ähnlich / similar picture

OVERLOAD RELAY, 7...10 A, 1NO+1NC,
 SIZE S00, CLASS 10,
 CAGE CLAMP CONNECTION,
 FOR INSTALLAT. AS A SINGLE UNIT


General technical details:

Operating current / of the fuse link / rated value	35 A
Adjustable response current / of the current-dependent overload release / initial value	7 A
Adjustable response current / of the current-dependent overload release / final value	10 A
Service power / for three-phase servomotors / rated value	4 kW
Number of NC contacts / for auxiliary contact	1
Number of NO contacts / for auxiliary contact	1
Number of change-over switches / for auxiliary contact	0
Type of assignment	2
Type of protection	DMT 98 ATEX G 001

Mechanical design:

Design of the electrical connection / for main current circuit	Cage Clamp terminals
Design of the electrical connection / for auxiliary and control current circuit	Cage Clamp terminals
Size of the contactor / can be combined / company-specific	S00

Type of fixing/fixation	stand-alone installation
Size of overload relay	S00
Ambient conditions:	
Protection class IP	IP20



last change:

10/31/2006

Technical Assistance:

Telephone: +49 (0) 911-895-5900 (8°° - 17°° CET)

Fax: +49 (0) 911-895-5907

E-Mail: technical-assistance@siemens.com

Internet: www.siemens.de/lowvoltage/technical-assistance