



UNDERVOLTAGE RELEASE, AC 400V/50HZ,
AC 440V/60HZ W. SCREW CONNECTION;
FOR CIRCUIT-BREAKERS, SZ S00/S0

General technical data:

product brand name		SIRIUS
product designation		undervoltage release
Size of the circuit-breaker		S00, S0
Acceptability for application		motor circuit breaker
Protection class IP / on the front		IP20
Design of the short-circuit protection		fuse
Degree of pollution		3
Insulation voltage / rated value	V	690
Insulation voltage / with degree of pollution 3 / rated value	V	690
Ambient temperature		
• during storage	°C	-50 ... +80
• during operating	°C	-20 ... +60
Item designation		
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		F
• according to DIN EN 61346-2		F

Auxiliary circuit:

Number of NC contacts / for auxiliary contacts		
• instantaneous switching		0

Number of NO contacts / for auxiliary contacts • instantaneous switching		0
Number of NO contacts / for auxiliary contacts • leading switching		0
Number of changeover contacts / of the auxiliary contacts • instantaneous switching		0

Control circuit:

Type of voltage / of the controlled supply voltage		AC
Control supply voltage frequency • 1 / initial rated value • 1 / final rated value	Hz Hz	50 60
Control supply voltage • 1 / at 50 Hz / for AC / rated value • 1 / at 60 Hz / for AC / rated value	V V	400 440

Installation/mounting/dimensions:

Type of mounting		snap-on mounting
Width	mm	18.5
Height	mm	90
Depth	mm	68

Certificates/approvals:

Verification of suitability CE / UL / CSA

General Product Approval



CSA



UL



EG-Konf.

Declaration of Conformity

Test Certificates

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

Shipping Approval



ABS



BUREAU VERITAS



GL



LRS



PRS



RINA

Shipping Approval other



RMRS




VDE


[other](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>





last change:

Dec 17, 2012