SIEMENS

Product data sheet

3SE2912-2AB20

LATCHING FOOT-OPERATED SWITCH, SINGEL PEDAL, CABLE ENTRY M20X1,5 IP65, 1NO + 1NC, WITHOUT CAP



General technical details:				
Product designation		foot switch		
Product equipment / interlock		No		
Product equipment / notch		Yes		
Product component / covering		No		
Operating current / at AC-15 / at 230 V / rated value	А	16		
Number of switching steps		1		
Number of the activation pedals		1		
Reference code / according to DIN 40719 extended according to IEC 204-2 / according to IEC 750		S		
Reference code / according to DIN EN 61346-2		S		
Mounting type		screw fixing		
Enclosure:				
Material / of the enclosure		metal		
Color / of the housing		black		
Color / of top part of the enclosure		grey		
Color		grey-black		
Width	mm	70		
Height	mm	220		
Depth	mm	61		

Contact:							
Number of NC contacts / for auxiliary co	ontacts		1				
Number of NO contacts / for auxiliary co	ontacts		1				
Cable gland version			M20 x	1.5			
Ambient conditions:							
Protection class IP			IP65				
Ambient temperature / during operating	I	°C	80				
Ambient temperature / during operating	I	°C	-25				
Certificates/approvals:							
Suitability for use / safety cut-out switc	h		No				
General Product Approval	Declaration of Conformity						
SE ERE	EG-Konf.						
Shipping Approval				other			
ABS LRS	PRS	RINA		<u>Confirmation</u>	other		
Further information:							
Information- and Downloadcenter (Cata http://www.siemens.com/industrial-controls							
Industry Mall (Online ordering system) http://www.siemens.com/industrial-controls	s/mall						
CAx-Online-Generator http://www.siemens.com/cax							
Service&Support (Manuals, Certificates http://support.automation.siemens.com/W		-					
Image database (product images, 2D di http://www.automation.siemens.com/bilddl	_		circuit dia	agrams,)			

last change:

Jan 21, 2013