

# SIEMENS

## Product data sheet

**6AV6671-8XB10-0AX1**


SD CARD 512 MB FOR ALL MP177/277/377/ M.P.  
(MOBILE PANEL) 277 AND FROM WINCC  
FLEX.2008 SP1 F. OP77,  
TP/OP177-277, M.P.177 WITH SD/MMC SLOT

Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Supply voltage	
Type of supply voltage	DC
Rated voltage/DC	3.3 V
Input current	
Current consumption (rated value)	60 mA
Memory	
Type of memory	Secure Digital memory card
Size	512 Mbyte
Standards, approvals, certificates	
CE	Yes
Ambient conditions	
Operating temperature	

Operating temperature range, max.	50 °C
Operating temperature range, min.	0 °C
<b>Storage/transport temperature</b>	
Min.	-20 °C
max.	60 °C
<b>Relative humidity</b>	
max. relative humidity	90 %
<b>Mechanics/material</b>	
Type of housing (front)	
Plastic	Yes
<b>Dimensions</b>	
Width	24 mm
Height	32 mm
Thickness	2.1 mm
<b>Weight</b>	
Weight without packaging	3 g
<b>Scope of supply</b>	
Delivery unit in items	1
<b>other</b>	
Note:	For Mobile Panels 277, MP 177, MP 277, MP 377 and WinCC flexible 2008 SP1 and higher for OP 77, TP/OP 177/277, MP 177, with SD/MMC slot
Status	Jul 17, 2012