

SINAMICS G120 POWER MODULE PM240 WITHOUT FILTER WITH BULT IN BRAKING CHOPPER 3AC380-480V +10/-10% 47-63HZ OUTPUT HIGH OVERLOAD: 1,5KW FOR 200% 3S,150% 57S,100% 240S AMBIENT TEMP -10 TO +50 DEG C 173 X 73 X 145 (HXWXD), FSA PROTECTION IP20 WITHOUT CONTROL UNIT AND BOP

No Data Available

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.de/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>