

SIEMENS

Product data sheet

6SL3224-0BE31-5UA0

product name	PM240 IP20 FSD U 400V 15kW
Design	D
Back supply / [nicht versorgt - möglich]	No
rated output / kilowatt (kW)	15 kW
rated output / in Horse Power (HP)	20 hp
Input voltage / minimum	380 V
Input voltage / maximum	480 V
Line frequency	50 Hz
efficiency eta	95
Rated Input Current	40 A
Output current / for constant torque / rated value	32 A
Phase number / of the outputs	3
Electrical output frequency / maximum	650 Hz
type / [nicht versorgt - der Überlastbarkeit]	150% for 57s with 300s, 200% for 3s with 300s
Protection class IP	IP 20
Depth	0.204 m
Height	0.419 m
Width	0.275 m
weight	7 kg
Type of cooling	fan
cooling method / [nicht versorgt - Kühlkörper]	Aluminium
letzte Änderung:	Oct 25, 2010