ITEM (1) ITEM(2) ITEM (3) ITEM (4) PART NUMBER BODY CONTACT INSULATOR NUT BRASS ZINC CP-AD517 BRASS TEFLON NICKEL PLATED GOLD PLATED NICKEL PLATED


受控 CONTROLLED DOCUMENT 编号 CP-AD517 版本 Rev Rel'd Date Mar 24,08


D

С

В

DRAWING NO.





3


NOTES:

5

D

ELECTRICAL SPECIFICATIONS
IMPEDANCE: 75 OHMS NOMINAL
FREQUENCY RANGE: 0-2 GHz
WORKING VOLTAGE: 500 Vrms MAX AT SEA LEVEL
DIELECTRIC WITHSTANDING VOLTAGE: 1500 vrms AT SEA LEVEL
CORONA LEVEL:375 VOLTS MINIMUM AT 70,000 FEET
CONTACT RESISTANCE: OUTER-0.2 MILLIOHMS MAXIMUM
CENTER-2.1 MILLIOHMS MAXIMUM
INSULATION RESISTANCE: 5000 MEGOHMS MINIMUM

- 2. MECHANICAL SPECIFICATIONS DURABILITY: 500 CYCLES MIN
- 3. ENVIRONMENTAL SPECIFICATIONS RECOMMENDED TEMPERATURE RANGE: -55 ℃ TO +85℃ MOISTURE RESISTANCE: MIL-STD-202
- 4. PRODUCT SHOULD BE RoHS COMPLIANCE
- 5. PACKAGING REQUIREMENT FOLLOWS ENGINEERING DOCUMENT P/N 836-40200001XX.



THIS DRAWING TO BE INTERPRETED PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL

	TOLERANCE UNLESS OTHERWISE SPECIFIED			DATE 01-10-07	•		Connectivity	
	DECIMALS	mm	CHECKED BY	DATE		RSON. rk Power	Solution	ns
	Х	± 0.5	LINDA.WU	01-10-07	TITLE	IKTOWEI		
	X.X	± 0.2	APPROVED BY	DATE	75 OHM RCA JACK TO BNC PLUG,ADAPTER			
	X.XX	± 0.1	THOMAS	01-10-07				
Γ	ANGLES	± 0.5°	U/M mm	⊕ ⊟				
			PRODUCED BY VING OR UPDATE	COMPUTER,	SHEET 1 OF 1	CP-AD517		SIZE

4 3 2