

Protect It! 6-Outlet Low-Profile Surge Protector, Direct Plug-In, 540 Joules, Diagnostic LED

MODEL NUMBER: SK6-0



Highlights

- 6 outlets/direct plug-in
- 540 joule rating
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Personal computers, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, audio/visual devices, and more.

Package Includes

- SK6-0 Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0 Surge Suppressor from Tripp Lite is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 540 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 6 outlets; direct plug-in
- Surge energy absorption: 540 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Holds up to 4 large transformer plugs
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)



Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150V
AC Suppression Surge Current Rating	27,000 amps
UL1449 Let Through Rating	400, 500, 500
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.18 x 4.53 x 4.75
Shipping Dimensions (hwd / cm)	3 x 11.5 x 12
Shipping Weight (lbs.)	.55
Shipping Weight (kg)	.25
Unit Dimensions (hwd / in.)	4.80 x 4.35 x 1.42
Unit Dimensions (hwd / cm)	12.19 x 11.05 x 3.6
Unit Weight (lbs.)	.406
Unit Weight (kg)	.18
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Light Gray
Receptacle Color	Light Gray
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Metal Case	No
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.