

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

SHC1036CR -- Cord Connectors



Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue. They're available in N.P.

Product Specifications

| | |
|--|--|
| Product Type | Cord Connectors |
| Material/Style | Nylon Standard Style |
| Cord Diameter Range | .50"- .63" (12.7- 15.9) |
| Cord Connector Body Style | Straight Male |
| Form Size | F3 |
| HUB Size | 3/4" |
| Color Code | Brown |
| Effective Operating Temperature | -30°F to +225°F (-34°C to +107°C) |
| Recommended Knockout Hole Size | 1.09"- 1.14" (27.8-29.0) |
| Flammability | Hubbell nylon cord connectors have a UL 94-V2 rating. |
| Hazardous Locations | Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b). |
| Dimension A | 1.56" (39.6) Dia. |
| Dimension B | 1.60" (40.6) Ref. |
| Dimension C | .55" (14.0) |
| Dimension D | .77" (19.6) Throat Dia. |
| Dimension E A/C | 1.44" (36.6) |
| Dimension E A/F | 1.31" (33.3) |
| Certifications | UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111. |
| UPC Number | 78358520808 |
| Weight in LBs | 0.2 |
| Link to Drawing Library | Click here for Library |
| Link to PDF Catalog | Click here for Catalog |



