



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to IEC-320-C20), 6-ft.

MODEL NUMBER: **P036-006**



### Highlights

- C19 to C20 Power Cord, 6ft
- 12AWG x 3C, 20 Amp Rated
- RoHS Compliant

### Package Includes

- C19 to C20 Power Cord, 6ft.

### Description

Use Tripp Lite's P036-006 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20A rated, 250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cord, 6ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Compliant

## Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>