

## TAA-Compliant Protect It! 6-Outlet Surge Protector, 6-ft Cord, 790 Joules, Diagnostic LED

MODEL NUMBER: TLP606TAA



### Description

Tripp Lite's TLP606TAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. It offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP606TAA offers 6 total outlets, 6 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 790 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs offer convenient protection of desktop computer equipment and accessories. \$20,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/790 joules/330V UL1449 3RD EDITION

### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 6 outlets
- 6-ft. cord
- Surge suppression rating: 790 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers

### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 6 outlet / 6-ft. cord
- 790 joule rating
- \$20,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

### Package Includes

- TLP606TAA surge suppressor
- Instruction manual with warranty information



- Keyhole support for wall mounting
- Lighted power switch
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 3 transformers total
Outlet Orientation	Single row of 6 outlets
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	790
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150



UL1449 Let Through Rating	400V - UL Verified
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	12.20 x 4.72 x 1.49
Shipping Dimensions (hwd / cm)	30.99 x 11.99 x 3.78
Shipping Weight (lbs.)	1.16
Shipping Weight (kg)	0.53
Unit Dimensions (hwd / in.)	1.26 x 1.65 x 10.5
Unit Dimensions (hwd / cm)	3.20 x 4.19 x 26.67
Unit Weight (lbs.)	1.05
Unit Weight (kg)	0.48
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Color (AC Line Cord)	Gray
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>