HellermannTyton

Panel Thickness Min. (Imperial)0.07 "Panel Thickness Min. (Metric)1.7 mm

126-00086	
Art	ticle Number: 126-00086
Do	med Low Profile Mount Ties, 6.2" Long, Mounting Hole Diameter .25"26", PA66HS, Black, 500/pkg
HellermannTyton	RoHS
-	spec sheet
Base Data	
	126-00086
Туре	T50SOSKSFT6.5S2-E
	Black (BK)
Features and Benefits	 Dome provides a tight, rattle-free installation. Outside serrated strap has ribs designed for convoluted tubing. Dome acts as a seal to keep out dust and liquid.
Product Description	HellermannTyton's low profile push mount design provides an overall shortened length which assists in limiting protrusion on the opposing side of application surfaces. The rounded tip of the mount allows for a smoother surface i case of contact with surrounding components or human touch during service.
Short Description	Domed Low Profile Mount Ties, 6.2" Long, Mounting Hole Diameter .25"26", PA66HS, Black, 500/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225 N
Length L (Imperial)	6.2 "
Length L (Metric)	157.5 mm
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.6 mm
Height H (Imperial)	0.58 "
Bundle Diameter Min. (Imperial)	0.04 "
Bundle Diameter Min. (Metric)	1.0 mm
Bundle Diameter Max. (Imperial)	1.4 "
Bundle Diameter Max. (Metric)	35.0 mm
Disc Diameter (Imperial)	0.63 "
Disc Diameter (Metric)	16.0 mm
Panel Thickness Max. (Imperial)	0.09 "
Panel Thickness Max. (Metric)	2.3 mm
Panal Thickness Min (Imporial)	

Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "		
• • • • •			
Mounting Hole Diameter D (Metric)			
Mounting Hole Diameter D Min.	0.248 "		
(Imperial)	Mounting Hole Diameter D Max.0.264 "		
	(Imperial)	Thickness T (Imperial)0.05 "	
Mounting Hole Diameter D Max.	6.7 mm		
-			
(Metric) Mounting Hole Diameter D Min. (Metric)6.3 mm			
Thickness T (Metric)	1.3 mm		
Logistics and Packaging			
Quantity Per	bag		
Package Quantity (Metric)	500 Pieces		
Carton Quantity	5000 Pieces		
Weight (Metric)	1.3 kg		
Material and Specifications			
Material	Polyamide 6.6 heat stabilized (PA66HS)		
Material Shortcut	PA66HS		
Flammability	UL94 V2		
Operating Temperature	-40°F to +221°F (-40°C to +105°C)		

ROHS Compliant Yes

© HellermannTyton 2015