

151-01105

Article Number: 151-01105

High Torque Axial Mount, Bolt Hole Dia .327 in, PA66HIRHS, Black, 500/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 151-01105

Type SAM320B

Color Black (BK)

- Features and Benefits**
- Positions bundles off cross members and frame rails to prevent abrasion and chafing.
 - Metal insert bushing accommodates high torque installation.
 - Made with high impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.

Product Description HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.

Fixation Method (FF) Screw Mounting and Rivet

Short Description High Torque Axial Mount, Bolt Hole Dia .327 in, PA66HIRHS, Black, 500/pkg

Product Dimensions

Length L (Imperial) 1.18 "

Length L (Metric) 29.87 mm

Width W (Imperial) 0.96 "

Width W (Metric) 24.32 mm

Height H (Imperial) 1.77 "

Height H (Metric) 44.86 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.8 mm

Mounting Hole Diameter D (Imperial) 0.327 "

Mounting Hole Diameter D (Metric) 8.31 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 500

Material and Specifications

Material Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS compliant (Article 4 - 1) Yes

