



Molded Case Circuit Breakers

T&B Catalog Number:

TS3N070TW

UPC Number:

80432534719

Status:

Active

Description:

3 pole, 70 amps rated at 600V AC/DC, Tmax molded case circuit breaker with a thermal magnetic trip device and 25kA at 480V AC interrupt current rating

Features

Short circuit protection is provided by a precise magnetic coil

Advanced contact design and arcing chambers provide the latest in fault current protection

Application

For power distribution applications

Can be installed in either the horizontal or vertical planes

Suitable for reverse feed applications

General

Trip Type Thermal Magnetic

Number of Poles 3

Series TS3

Approvals

UL Class UL 489

Dimension Information

H x W x D (inches) 6.7 x 4.13 x 4.07

Specifications

Rated Current (Amps) 70

Rated Voltage AC 600

Rated Voltage DC 600

Interrupt Rating 25kA at 480V AC

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 6.48 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com