

Office Pro LCD

Orion Power Systems

Cost Effective Power Protection from 1000VA to 2000VA



The Orion Power Systems Office Pro LCD is the most cost effective solution for protecting small/home office computers, telephone, security, and peripheral equipment.

Ideally suited for:

- Point of Sale
- Security Systems
- Data processing
- Phone Systems
- Peripherals

Product Snapshot

Power Rating	1000VA/600W 1400VA/840W 2000VA/1200W
Input Voltage Range	120 VAC (Nominal)
Output Voltage Range	120 VAC (Nominal)
Frequency (HZ)	50/60 HZ
Topology	Line Interactive
Configuration	Tower

Battery Backup time in Minutes

Load (VA/Watts)	Internal Batteries	Typical computer load *
OP1000U-LCD		
1000/600	5 min.	61 min.
OP1400U-LCD		
1400/840	4 min.	85 min.
OP2000U-LCD		
2000/1200	2 min.	85 min.

* Runtimes listed are at full watt load. Typical computer load is 100 watts. Calculations are approximate and will vary based on battery age, temperature, etc.

Features

- LCD Display
- Automatic Voltage Regulation
- Line Interactive Design
- Modem/LAN Internet Protection
- USB Communication Port
- Power Monitoring and Shutdown Software
- Surge Protection with Noise Filtering
- Self Test and Self Diagnostics
- Smart Battery Management
- 37 Month Silver Warranty on Electronics and Batteries
- Lifetime \$50,000 Load Protection Guarantee



LCD Display

State of the Art LCD display provides real time status information of Volts in, Volts out, battery percentage remaining, percentage load, and more. All the information you need at a glance.



Industry Leading Warranty and Protection



Orion Power Systems 37 Month Silver Warranty

Orion Power Systems offers the longest standard warranty in the industry – an exclusive 37 month electronics / 37 month battery warranty.



Ultimate 860 Joules Surge Protection Rating

Office Pro uses MOV (Metal Oxide Varistor) technology to provide your connected equipment the maximum protection against transients, surges and spikes. It uses an array of MOVs to provide 860 joules capacity – more than twice the protection of competitors. The Office Pro series also protects against back door threats with built-in RJ45 surge protection.



Lifetime \$ 50,000 Load Protection Guarantee

Protect your valuable equipment with \$ 50,000 coverage protection from spikes, surges, and transients. Unlike many other manufacturers of ups systems, Orion Power Systems guarantee is good for the lifetime of the UPS.



OFFICE PRO LCD 1K/1.4K/2K LINE INTERACTIVE UPS SELECTION GUIDE

MODEL	OP1000U-LCD	OP1400U-LCD	OP2000U-LCD
CAPACITY	1000 VA / 600 W	1400 VA / 840 W	2000 VA / 1200 W
INPUT			
Voltage	120 VAC with 5-15P		120 VAC with 5-20P
Voltage Range	81-145 VAC		
Frequency Range	50/60 Hz (auto sensing)		
OUTPUT			
Output Voltage	120 VAC		
AC Voltage Regulation (Batt. Mode)	+/- 10%	+/- 5% at load < 50%	
Frequency Range (Batt. Mode)	50 Hz or 60 Hz ±1 Hz		
Transfer Time	2-6ms	4-8ms	
Receptacles	(8) UPS	(8) UPS	(8) UPS
Waveform	AC Input (True Sine Wave) / Battery Mode (Simulated Sine Wave)		
BATTERY			
Battery Type & Number	12 V/7 AH x 2	12 V/9 AH x 2	12 V/9 AH x 2
Typical Recharge Time	10 hours to 90%	6 hours to 90%	
INDICATORS			
LCD Display	AC Mode, Battery Mode, Load Level, Battery Level, Input Voltage, Output Voltage, Overload, Fault, and Low Battery		
Battery Mode / Low Battery	Sounding every 10 seconds / Every second		
Overload	Sounding every 0.5 second		
Battery Replacement Alarm	Sounding every 2 seconds		
Fault	Continuously sounding		
PROTECTION			
Full Protection	Overload, discharge, and overcharge protection		
Surge Protection	860 joules		
PHYSICAL			
Dimension, D X W X H (inches)	15.9 x 5.7 x 8.07		
Net Weight (lbs)	21.4 lbs.	26.5 lbs.	26.5 lbs.
OPERATING ENVIRONMENT			
Humidity / Noise Level	0-90 % RH @ 0- 40°C (non-condensing) / Less than 45dB		
MANAGEMENT			
USB Port	Supports Windows family, Linux, IBM, Aix, Sun Solaris, Compaq True 64, UnixWare, FreeBSD, HP-UX, and MAC.		
COMPLIANCE	UL1778, FCC		



Orion Power Systems, Inc.
 3811 University Blvd. # 3
 Jacksonville, FL 32217
 Toll-Free: 877.385.1654
 Web: orionpowersystems.com