






Professionally approved products.

Socket Sets

30 Pc Screwdriver Bit & Nut Driver Set



RS Stock No. 213-1005

Kit Contents						
Pieces in set	Metric sockets (mm)	Hexagon bits 25mm long (mm)	Pozidriv bits 25mm long	Slotted bits 25mm long (mm)	Slotted bits 50mm long (mm)	Torx bits 25mm long
30	5, 6, 7, 8, 9, 10, 11	2, 3, 4, 5, 6, 7	Pz0, Pz1, Pz2, Pz3	3, 5, 8	6	Tx10, Tx15, Tx20, Tx25, Tx30, Tx40
Type of Bit						



Material

For bits: Chrome Molybdenum Steel (S-2)

For nut drivers: Chrome Vanadium Steel and zinc alloy with carbon steel for shaft of bit holder

Finish

Chrome plated for bit holder

Sandblasted finish for bits & nut drivers

Hardness

Heat treated to HRC: 56 ~ 62 Degree for bits

HRC: 42 ~ 48 Degree for nut drivers

Contents

7 pcs -1/4" dr. Hexagon shaft nut drivers (Metric): 5, 6, 7, 8, 9, 10 and 11mm

1 pc - 60 mm (2-1/4") Magnetic bit holder with Quick change connector

18 pcs - 25 mm (1") screwdriver bits with:

1/4" Hexagon shank

Slotted: 3, 5 and 8 mm

Pozdriv: No. 0, No. 1 and No. 3

Hex bits: 2, 3, 4, 5, 6 and 7 mm

Torx driver: t-10, t-15, t-20, t-25, t-30 and t-40

2 pcs - 50 mm (2") Power bits with 1/4" Hexagon shank & Quick change connector:

Slotted: 6 mm

Pozdriv: No. 2

2 pcs - Screw finders (nylon with spring bit holders)